

### 3D Implant Abutment Compatible Chart

Implant Brand	Type	ScrewDriver	Titanium	Zirconia	Screw		Hybrid(3-piece)	Screw
			available	available	Brand	Screw mode	3D Screw	available
<b>3i</b>	Certain3.4	Hex 0.048"	●	not available	IUNITS	HEX048-1667	●	HEX048-1675
	Certain4.1	Hex 0.048"	●	not available	IUNITS	HEX048-1667	●	HEX048-1675
	Certain5.0	Hex 0.048"	●	not available	IUNITS	HEX048-1667	●	HEX048-1675
	Certain6.0	Hex 0.048"	●	not available	IUNITS	HEX048-1667	●	HEX048-1675
	External3.4	Hex 0.048"	●	●	MUNITS	HEX048-2062	not available	
	External4.1	Hex 0.048"	●	●	UNITS	HEX048-2062	not available	
	External5.0	Hex 0.048"	●	●	UNITS	HEX048-2062	not available	
	External6.0	Hex 0.048"	●	●	UNITS	HEX048-2062	not available	
<b>Astra</b>	OsseoSpeed 3.5/4.0	Hex 0.05"	●	not available	24449	HEX050-1660	●	HEX050-1665
	OsseoSpeed 4.5/5.0	Hex 0.05"	●	not available	24209	HEX050-2082	●	HEX050-2095
	Fixture MT 3.5	Hex 0.05"	not available	not available	24208(M1.4)		not available	
	Fixture MT 4.0	Hex 0.05"	not available	not available	24209(M2)		not available	
	Fixture MT 4.5/5.0	Hex 0.05"	not available	not available	24209(M2)		not available	
<b>Nobelbiocare Branemark</b>	NP	UniGrip	●	●	31168	UGN-1654	not available	
	RP	UniGrip	●	●	29290	UGN-2057	not available	
	WP	UniGrip	●	●	31169	UGN-2557	not available	
<b>Nobelbiocare Replace</b>	NP	UniGrip	●	not available	31170	UGN-1866	●	UGN-1872
	RP	UniGrip	●	not available	29293	UGN-2084	●	UGN-2090
	WP	UniGrip	●	not available	29293	UGN-2084	●	UGN-2090
	6.0	UniGrip	●	not available	29293	UGN-2084	●	UGN-2090
	Active NP	UniGrip	●	not available	29282	UGN-1654		
	Active RP	UniGrip	●	not available	29283	UGN-2057		
<b>Straumann</b>	NN	UniGrip	●	●	049.177	UGS-1836	not available	
	RN	UniGrip	●	not available	048.356	UGS-2046	●	UGS-2065
	Wn	UniGrip	●	not available	048.356	UGS-2046	●	UGS-2065
	NC	UniGrip	●	not available	25.2906	UGS-1670	not available	
	RC	UniGrip	●	not available	25.4906	UGS-1670	not available	
<b>Zimmer</b>	Tapered Screw-vent 3.5	Hex 0.05"	●	not available	MHLAS	HEX050-1858	●	HEX050-1862
	Tapered Screw-vent 4.5	Hex 0.05"	●	not available	MHLAS	HEX050-1858	●	HEX050-1862
	Tapered Screw-vent 5.7	Hex 0.05"	●	●	MHLAS	HEX050-1858	●	HEX050-1862
	Spline 3.25	Hex 0.05"	●	●	1537	HEX050-1858	not available	
	Spline 3.75/4.0	Hex 0.05"	●	●	1537	HEX050-1858	not available	
	Spline 5.0	Hex 0.05"	●	●	1537	HEX050-1858	not available	
<b>BioHorizons</b>	External 3.5	Hex 0.05"	●	●	130-300	HEX050-1858	not available	
	External 4.0	Hex 0.05"	●	●	140-300	HEX050-2056	not available	
	External 5.0	Hex 0.05"	●	●	140-300	HEX050-2056	not available	
	External 6.0	Hex 0.05"	●	●	140-300	HEX050-2056	not available	
	Internal 3.5	Hex 0.05"	●	not available	PXAS	HEX050-1848	●	HEX050-1862
	Internal 4.5	Hex 0.05"	●	not available	PXAS	HEX050-1848	●	HEX050-1862
	Internal 5.7	Hex 0.05"	●	not available	PXAS	HEX050-1848	●	HEX050-1862
<b>Friadent Xive</b>	Frialit 3.0	Hex 0.048"	●	not available	46-430499	HEX048-1468	not available	
	Frialit 3.4	Hex 0.048"	●	not available	46-430599	HEX048-1667	●	HEX048-1675
	Frialit 3.8	Hex 0.048"	●	not available	46-430599	HEX048-1667	●	HEX048-1675
	Frialit 4.5	Hex 0.048"	●	not available	46-430599	HEX048-1667	●	HEX048-1675
	Frialit 5.5	Hex 0.048"	●	not available	46-430599	HEX048-1667	●	HEX048-1675
	Frialit 6.5	Hex 0.048"	●	not available	46-430599	HEX048-1667	●	HEX048-1675
<b>Lifecore</b>	External Hex SD	Hex 0.048"	●	●	R9203-34-48	HEX048-1860	not available	
	External Hex RD	Hex 0.048"	●	●	R9202-40-48	HEX048-2065	not available	
	External Hex WD	Hex 0.048"	●	●	R9203-50-48	HEX048-2566	not available	
	Internal Hex SDI	Hex 0.048"	●	not available	43116	HEX048-1860	●	HEX048-1872
	Internal Hex RDI 4.5/4.75	Hex 0.048"	●	not available	43116	HEX048-1860	●	HEX048-1872
<b>Osstem</b>	US Mini (3.5)	Hex 0.048"	●	not available	ASM200		not available	
	US Regular (4.1)	Hex 0.048"	●	not available	ASR200	HEX048-2065	not available	
	US Wide (5.1)	Hex 0.048"	●	not available	ASM200		not available	
	SS Regular (4.8)	Hex 0.048"	●	not available	ASR200	HEX048-2065	not available	
	SS Wied (6.0)	Hex 0.048"	●	not available	ASR200	HEX048-2065	not available	
	GS Mini (3.5)	Hex 0.048"	●	not available	GSASM	HEX048-1682	not available	
	Gs Standard (4.0/4.5/5.0)	Hex 0.048"	●	not available	GSASR	HEX048-2065	not available	

For Hybrid(3-piece) abutment, use 3D screw only